



BTC380E



Earth leakage add-on-block 3P 125A Adjustable type AC

Technical properties

Architecture

Neutral position	Left or right
Number of poles	3 P

Configuration

Number of modules	6
-------------------	---

Connectivity

Top connection alignment for modular devices	Not applicable
Bottom connection alignment for modular devices	Aligned terminal

Main electrical features

Rated operational voltage U_e	415 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

Electric current

Rated residual operating current	300 mA / 500 mA / 1 A
Rated current	125 A

Electric current / temperature

Rating current 20°C	125 A
Rating current 30°C	125 A
Rating current 40°C	118.9 A
Rating current 50°C	112.4 A
Rating current 60°C	105.6 A
Rating current 70°C	99.4 A

Dimensions

Depth of installed product	69 mm
Height of installed product	103 mm
Width of installed product	187 mm

Power

Total power loss under I_N	11.25 W
------------------------------	---------

Tripping

Protected against nuisance tripping	No
Short-time delayed tripping	No
Endurance	
Electric endurance in number of cycles	1000
Number of mechanical operations	7000
Installation, mounting	
Tightening torque	3,5Nm
Type of top rail clip for modular devices	NA
Type of bottom rail clip for modular devices	metallic
Type of Bottom Connection for modular devices	with screw
Top removability for modular devices	No
Bottom removability for modular devices	Yes
Connection	
Connection cross-sect. flexible conductor	10 - 50 mm ²
Connection cross-sect. rigid cable	10 / 70 mm ²
Settings	
Rated fault current adjustable	Yes
Delay adjustable	Yes
Time delay of residual current	0 / 60 / 150 ms
Standards	
Standard text	IEC 61009-1 ; EN 61009-1
Safety	
Residual current type	AC
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Air humidity protection	for all climates