



BN464

## Earth leakage add-on block 4P 63A 100mA AC S Class

### Technical properties

#### Architecture

Neutral position	left
Number of poles	4 P

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	100 mA
Rated current	63 A

#### Electric current / temperature

Rating current 40°C	63 A
---------------------	------

#### Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

#### Frequency

Frequency	50 Hz
-----------	-------

#### Tripping

Protected against nuisance tripping	No
Short-time delayed tripping	Yes

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

#### Installation, mounting

Tightening torque	2,8Nm
Type of top rail clip for modular devices	Plastic
Type of bottom rail clip for modular devices	NA
Top removability for modular devices	Yes
Bottom removability for modular devices	No

**Connection**

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
Connection cross-sect. rigid cable	25mm <sup>2</sup>

**Settings**

Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0.3 s

**Safety**

Residual current type	AC SEL
REACH conform	No
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-5...40 °C
Altitude	2000 m
Air humidity protection	Execution I