



BS363

**Earth leakage add-on block 3P 63A 1A A S Class**

**Technical properties**

**Architecture**

Neutral position	left
Number of poles	3 P

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	1 A
Rated current	63 A

**Electric current / temperature**

Rating current 40°C	63 A
---------------------	------

**Dimensions**

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

**Frequency**

Frequency	50 Hz
-----------	-------

**Power**

Total power loss under IN	7.5 W
---------------------------	-------

**Tripping**

Protected against nuisance tripping	No
Short-time delayed tripping	Yes

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

**Installation, mounting**

Tightening torque	2,8Nm
Type of top rail clip for modular devices	Plastic

Type of bottom rail clip for modular devices	NA
Top removability for modular devices	Yes
Bottom removability for modular devices	No

---

**Connection**

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
---	-------------------

---

**Settings**

Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0.3 s

---

**Standards**

European directive WEEE	concerned
-------------------------	-----------

---

**Safety**

Protection index IP	IP20
Residual current type	A SEL

---

**Use conditions**

Operating temperature	-5...40 °C
Altitude	2000 m