



DR80F



Din rail board, 5 row 80M, non-transparent door, flush

Technical properties

Architecture

Intended door position	left
------------------------	------

Configuration

Number of modules	80
-------------------	----

Compatibility

Suitable for lightning protection	Yes
-----------------------------------	-----

Dimensions

Insertion depth	110 mm
Depth of wall niche	105 mm
Depth of installed product	5 mm
Internal depth	107 mm
Height of installed product	949 mm
Installation height	920 mm
Width of installed product	430 mm
Width in division units	16
Thickness of sidewall material	1.2 mm
Built-in width	400 mm

Cover, door

Material thickness cover	1.2 mm
Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

Materials

Copper weight of the product	0 kg
Colour	light grey
Material quality	Steel
Surface appearance	matt

Installation, mounting

Suitable for outdoor use	No
Suitable for ground mounting	No

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	5
Number of keys	1
Quantity of rails	5
On/Off switch	No
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	Yes

Standards

Approvals	BS EN 61439-3
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	IK05
Protection class	isol.class I
Glow wire test	according to IEC 61439-1
Halogen free	No
Fire resistance	-