



ECM140D

1 Phase kWhmeter direct 40A 1M MBUS MID

Technical properties

Architecture

Number of poles	2 P
Fixing mode	DIN rail type O (symmetrical)

Functions

Tarif type	- / T1...T2 M-BUS
------------	-------------------

Configuration

Number of modules	1
-------------------	---

Compatibility

Suitable for	Purchase / supply
--------------	-------------------

Main electrical features

Rated operational voltage Ue	92 / 276 V
Type of supply voltage	AC
Frequency	50 Hz

Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

Electric current

Minimum operating current	0.02 A
Operating current	0.02 / 40 A
Rated current	40 A
Reference current	5 A
Max. measurement circuit current	40 A

Dimensions

Depth of installed product	60 mm
Height of installed product	92 mm
Width of installed product	18 mm

Power

Power consumed	2 VA
Total power loss under IN	1 W

Electrical specifications

Type of pulse generator	optical
-------------------------	---------

Measurement	
Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electronical
Principle of measurement	Direct measurement
Installation, mounting	
Mounting type	din-Rail
Connection	
Wire cross section of metering entrance wire	16 mm ²
Wire cross section of metering outgoing wire	16 mm ²
Equipment	
Type of display	LCD
Type of counter	single-phase counter
Standards	
Standard text	EN 50470-1 / 3 ; IEC 62053-21 / 23 ; IEC 61557-12
European directive WEEE	concerned
Safety	
Protection index IP	IP20
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Use conditions	
Operating temperature	-25...55 °C
Altitude	2000 m
Storage/transport temperature	-25...70 °C