



ECM310D

3 Phase kWhmeter direct 125A 6M MBUS MID

Technical properties

Architecture

Number of poles	4 P
Fixing mode	DIN rail type O (symmetrical)

Functions

Tarif type	T1...T2 (230V AC) / T1...T2 M-BUS
------------	-----------------------------------

Configuration

Number of modules	6
-------------------	---

Compatibility

Suitable for	Purchase / supply
--------------	-------------------

Main electrical features

Rated operational voltage Ue	92 / 480 V
Type of supply voltage	AC
Frequency	50 Hz

Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

Electric current

Minimum operating current	0.02 A
Operating current	0.02 / 125 A
Rated current	125 A
Reference current	5 A
Max. measurement circuit current	125 A

Dimensions

Depth of installed product	60 mm
Height of installed product	92 mm
Width of installed product	107 mm

Power

Power consumed	2 VA
Total power loss under IN	0.6 W

Electrical specifications

Type of pulse generator	optical
-------------------------	---------

Measurement

Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electronical
Principle of measurement	Direct measurement

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Wire cross section of metering entrance wire	50 mm ²
Wire cross section of metering outgoing wire	50 mm ²

Equipment

Type of display	retro illuminated display
Tariff model of kilowatt-hour meter	Externa
Type of counter	4 wires counter

Standards

Standard text	EN 50470-1 / 3 ; IEC 62053-21 / 23 ; IEC 61557-12
European directive WEEE	concerned

Safety

Protection index IP	IP20
Protection class	isol.class II

Use conditions

Operating temperature	-25...55 °C
Altitude	2000 m
Storage/transport temperature	-25...70 °C