



CZ001

**Auxiliary contact for RCCB 2(1C+1O) 6A 240V AC**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	230 / 440 V
------------------------------	-------------

Frequency	50 Hz
-----------	-------

**Voltage**

Rated insulation voltage	500 V
--------------------------	-------

Rated operational voltage in DC	12 / 250 V
---------------------------------	------------

**Electric current**

Acceptable current rating with AC1	6 A
------------------------------------	-----

Rated current	6 A
---------------	-----

I <sub>min</sub> = f (U = 230 V AC)	6 A
-------------------------------------	-----

I <sub>min</sub> = f (U = 230 V DC)	0.6 A
-------------------------------------	-------

I <sub>min</sub> =f(U=400V AC) for power circuit	3 A
--	-----

**Dimensions**

Width of installed product	18 mm
----------------------------	-------

**Power**

Total power loss under I <sub>N</sub>	0.1 W
---------------------------------------	-------

**Endurance**

Electric endurance in number of cycles	6000
--	------

Number of mechanical operations	12000
---------------------------------	-------

**Installation, mounting**

Factory fitted	No
----------------	----

**Equipment**

Quantity of NC contacts	1
-------------------------	---

Quantity of NO contacts	1
-------------------------	---

Quantity of INV contacts	0
--------------------------	---

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Use conditions**

---

Operating temperature	-25...60 °C
Storage/transport temperature	-40...80 °C

---