



1 Phase kWhmeter direct 3x80A 4M MODBUS

Technical properties

Architecture	MODBUS
Bus system Number of poles	2 P
Type of pole	3x 1P+N
Functions	
Precision class	В
Tarif type	T1T2 (230V AC) / T1T4 Modbus
Configuration	
Number of modules	4
Compatibility	
Suitable for	Purchase / supply
Main electrical features	
Rated operational voltage Ue	92 / 276 V
Type of supply voltage	AC
Frequency	50 Hz
Voltage	
Max operating voltage	300 V
Rated impulse withstand voltage	6 kV
Electric current	
Minimum operating current	0.015 A
Operating current	0.015 / 80 A
Rated current	A 08
Reference current	5 A
Max. measurement circuit current	80 A
Dimensions	
Depth of installed product	60 mm
Height of installed product	92 mm
Width of installed product	72 mm
Power	
Power consumed	2 VA
Total power loss under IN	1 W

Electrical specifications

Type of pulse generator	optical
Measurement	
Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electronical
Principle of measurement	Direct measurement
Power supply	
Supply voltage	230 V ± 20%
Installation, mounting	
Tightening torque	2Nm
Mounting type	din-Rail
Connection	
Wire cross section of metering entrance wire	33 mm²
Wire cross section of metering outgoing wire	33 mm²
Equipment	
Type of display	retro illuminated display
Tariff model of kilowatt-hour meter	Externa
Type of counter	three-point system
Standards	
Standard text	IEC 62053-21 / 23 ; IEC 61557-12
Safety	
Protection class	isol.class II
Halogen free	No
Use conditions	
Operating temperature	-2555 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-2570 °C