



EC100

Hours counter

Technical properties

Configuration

Number of modules	2
-------------------	---

Main electrical features

Frequency	50 Hz
-----------	-------

Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	35 mm
Front plate height	90 mm
Front plate width	35 mm

Power

Total power loss under IN	1.5 W
---------------------------	-------

Power supply

Supply voltage	230 V +/- 15%
----------------	---------------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw

Equipment

Reading unit	1 h
Digits number	6

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...45 °C
Storage/transport temperature	-20...60 °C