



EC100

Hours counter

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Number of modules	2
-------------------	---

Main electrical features

Frequency	50 Hz
-----------	-------

Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	35 mm
Front plate height	90 mm
Front plate width	35 mm

Power

Total power loss under IN	1.5 W
---------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Equipment

Reading unit	1 h
Digits number	6

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...45 °C
Storage/transport temperature	-20...60 °C