



EE180



IP20

Astronomical Timeswitch 1 Channel

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Functions

Number of function channels	1
-----------------------------	---

Configuration

Number of modules	2
-------------------	---

Controls and indicators

Function of the pushbutton	yes
Indication / display	LC display with illumination

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Acceptable current rating with AC1	16 A
Max. power with cos phi 0.6	10 A
Switching current at cos ϕ = 0.6	max. 10 A

Dimensions

Depth of installed product	65 mm
Height of installed product	85 mm
Length	35 mm
Width of installed product	65 mm
Width of rail mounted device (RMD)	2 modules

Frequency

Frequency range	50...60 Hz
-----------------	------------

Power

Max. power with fluo uncompensated lamps	1000 VA
Power consumed	6 VA
Incandescent bulb power	0 / 2300 W
Total power loss under IN	2 W
Loss power at full load	≈ 2 W
Power dissipation per coil	0.3 W
Max. Breaking capacity for parallel compensated fluorescent tubes	400 W

Max. Breaking capacity for row-compensated fluorescent tubes	1000 W
--	--------

Battery

Power reserve [years]	≈ 5 a
-----------------------	-------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	400 VA
Max. power fluo. duo lamp comp. series	1000 W
Fluorescent lamps parallel compensated	400 VA

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
230 V incandescent lamps and halogen lamps	max. 2300 W

Installation, mounting

Mounting type	din-Rail
Installation mode	for mounting on DIN rail

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Conductor cross-section (flexible)	1...6 mm ²
Conductor cross-section (rigid)	1...6 mm ²
Number of contacts	1
Type of connection	with screw terminals

Settings

Number of program steps	56
Summer / Winter time change	automatic
Shortest switching time	1 mn
Astro program	Yes
Time	with automatic summer/winter time change-over

Equipment

Number of channels	1
Number of switching times for on/off	56
ON / OFF override	0
Supply failure reserve	5 years
With cyclic program	Yes
With holidays program	No
With random program	No

Use

Cycle	weekly
-------	--------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

Working accuracy	1,5
Storage/transport temperature	-20...60 °C