



EE181

IP20

## Astronomical Time switch, 2 Channels

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Functions

Number of function channels	2
-----------------------------	---

#### Configuration

Number of modules	2
-------------------	---

#### Controls and indicators

Function of the pushbutton	yes
----------------------------	-----

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Operating voltage	230 V~ +/- 15%
-------------------	----------------

#### Electric current

Acceptable current rating with AC1	16 A
------------------------------------	------

Max. power with cos phi 0.6	10 A
-----------------------------	------

Switching current at cos $\varphi$ = 0.6	max. 10 A
--	-----------

#### Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Length	35 mm
--------	-------

Width of installed product	3.5 mm
----------------------------	--------

Width of rail mounted device (RMD)	2 modules
------------------------------------	-----------

#### Frequency

Frequency range	50...60 Hz
-----------------	------------

#### Power

Max. power with fluo uncompensated lamps	1000 VA
--	---------

Power consumed	6 VA
----------------	------

Incandescent bulb power	0 / 2300 W
-------------------------	------------

Total power loss under IN	2 W
---------------------------	-----

Loss power at full load	≈ 2 W
-------------------------	-------

Power dissipation per coil	0.3 W
----------------------------	-------

Max. Breaking capacity for parallel compensated fluorescent tubes	400 W
Max. Breaking capacity for row-compensated fluorescent tubes	1000 W
<b>Measurement</b>	
Running accuracy	± 1.5 s/day
<b>Battery</b>	
Power reserve [years]	≈ 5 a
<b>Power supply</b>	
Supply voltage	230 V
<b>Fluorescent bulbs control</b>	
Max. power with fluorescent parallel lamps	400 VA
Max. power fluo. duo lamp comp. series	1000 W
Fluorescent lamps parallel compensated	400 VA
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	2300 W
230 V incandescent lamps and halogen lamps	max. 2300 W
<b>Installation, mounting</b>	
Mounting type	din-Rail
Installation mode	for mounting on DIN rail
<b>Connection</b>	
Conductor cross-section (flexible)	1...6 mm <sup>2</sup>
Conductor cross-section (rigid)	1...6 mm <sup>2</sup>
Number of contacts	2
Type of connection	with screw terminals
<b>Settings</b>	
Number of program steps	56
Summer / Winter time change	automatic
Shortest switching time	1 mn
Astro program	Yes
<b>Equipment</b>	
Number of channels	2
Number of switching times for on/off	56
ON / OFF override	0
Supply failure reserve	5 years
With cyclic program	Yes
With holidays program	No
With random program	No
<b>Use</b>	
Cycle	weekly

**Safety**

---

Protection index IP	IP20
---------------------	------

**Use conditions**

---

Operating temperature	-10...55 °C
-----------------------	-------------

---

Working accuracy	± 1,5 s / 24H
------------------	---------------

---

Storage/transport temperature	-20...60 °C
-------------------------------	-------------

**Identification**

---

Main design line	Light control
------------------	---------------