




EE805A



IP21

## Movement detector 360° flush mounted with normally open contact

### Technical properties

#### Functions

Function can only be used as individual unit

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50/60 Hz

#### Voltage

Operating voltage 230 V ~ +10%/-15%

#### Electric current

Switching current (ohmic) max. 10 A

#### Dimensions

Height of installed product 15.5 mm

Width of installed product 19 mm

Installation opening  $\varnothing$  75 mm

Assembling height 61 mm

Recommended installation height 2.5...3.5 m

Installation wall thickness 5...20 mm

#### Power

Halogen switching capacity 230V 0 / 1000 W

Max. power with fluo uncompensated lamps 1000 VA

Power consumption (standby) 0.3 W

Incandescent bulb power 0 / 1000 W

Maximum power per output for low-voltage halogen lamps with conv. transformer 500 W

#### Power supply

Supply voltage 230 V +10% / -15%

#### Detection

Detection angle 360 °

Detection field  $\varnothing$ , on floor  $\approx$  6 m

#### Materials

Colour white

#### Lighting control

Response brightness, adjustable  $\approx$  5...1000 lx

Brightness measurement range	5 / 1000 Lux
Fluorescent lamps with electronical ballast (EB)	8 x 58 W
<b>Fluorescent bulbs control</b>	
Energy-saving lamps	10 x 20 W
Fluorescent lamps uncompensated	1000 W
<b>Incandescent bulbs control</b>	
12 V halogen lamps	500 VA
<b>Installation, mounting</b>	
Maximum Mounting Height	4 m
Mounting type	flush-mounted
Installation mode	for ceiling mounting ; with spring clips for ceiling installation
<b>Connection</b>	
Conductor cross-section	1...2.5 mm <sup>2</sup>
Type of contacts	1NC
Type of connection	with screw terminals
<b>Settings</b>	
Response value sensitivity adjustable	No
Delay time, adjustable	5 s...30 mn
Setting	with potentiometers for setting the response brightness and delay time without dismantling
<b>Scope of delivery</b>	
Component	with fitting material
<b>Equipment</b>	
Potential-free	with potential-free normally-open contact
<b>Safety</b>	
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Operating temperature	0...45 °C
Storage/transport temperature	-20...60 °C
Energy-saving	energy saving by means of presence and brightness-dependent ON and OFF switching of light ; low intrinsic energy requirement
<b>Identification</b>	
Application, usage	Motion detector
Main design line	Motion detectors