




EE851



IP55

Motion detector comfort 140° anthracite

Technical properties

Architecture

Fixing mode surface-mounting

Main electrical features

Frequency 50/60 Hz

Dimensions

Height of installed product 2.5 mm

Recommended installation height 2.5 m

Reach distance

Range, side each ≈ 6 m

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 140 °

Detection angle 140 °

Frontal detecting distance 16 m

Side detecting distance 10 m

Materials

Colour charcoal

Material plastic

Lighting control

Response brightness, adjustable ≈ 5...1000 lx

Brightness measurement range 5 / 1000 Lux

Installation, mounting

Maximum Mounting Height 4 m

Connection

Type of connection with screw terminals

Settings

Response value sensitivity adjustable Yes

Delay time, adjustable 5 s...30 mn

Scope of delivery

Component with fitting material

Equipment

Remote controllable	EE806
Angle of horizontal detection	140 °
Slewing	vertically slewing and horizontally rotating

Safety

Protection index IP	IP55
---------------------	------

Use conditions

Operating temperature	-20...55 °C
Storage/transport temperature	-20...60 °C

Identification

Application, usage	Motion detector
Main design line	Motion detectors
