



EE635

## LED floodlight 700 Lumen, white

### Technical properties

#### Functions

Dimmer RF	No
Dimming 0-10 V	No
Dimmer DMX	No
Dimming GPRS	No
Dimming Zigbee	No
Dimming depending on control gear	No
Dimming LineSwitch	No
Dimming mains voltage modulation	No
Dimming potentiometer (integrated)	No
Dimming programmable	No
Dimming sine wave reduction	No

#### Main electrical features

Rated voltage	230...240 V
Type of supply voltage	AC

#### Dimensions

Height of installed product	140 mm
Length	100 mm
Built-in width	0 mm

#### Power

System rated power	8 W
--------------------	-----

#### Power supply

Control gear type	Not required
-------------------	--------------

#### Materials

RAL colour	RAL 9010 - Pure white
Material	plastic
Dominant light colour	white

#### Lighting control

Type of lamp	LED not exchangeable
Lamps capacity	8
Luminous flux	700 lm

#### Installation, mounting

Suitable for ground mounting	No
------------------------------	----

Suitable for clamp-mounting	No
Suitable for light-track mounting	No
Can be suspended	No
Suitable for traverse mounting	No
<b>Connection</b>	
Suitable for through-wiring	Yes
<b>Scope of delivery</b>	
With lamp	Yes
Control gear included	No
<b>Accessories included</b>	
With light sensor	No
<b>Equipment</b>	
Type of dimmer	Yes
Colour rendering index (CRI)	80-89
<b>Use</b>	
Beam angle	$\geq 80^\circ < 360^\circ$
Light sharing	Symmetric
<b>Safety</b>	
Protection index IP	IP55
Protection class	isol.class II