



EE851



IP55



Motion detector comfort 140° anthracite

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Height of installed product	2.5 mm
Recommended installation height	2.5 m

Reach distance

Range, side	each ≈ 6 m
-------------	------------

Power supply

Supply voltage	230 V +10% / -15%
----------------	-------------------

Detection

Detection angle	140 °
Detection angle	140 °
Frontal detecting distance	16 m
Side detecting distance	10 m

Materials

Colour	charcoal
Material	plastic

Lighting control

Response brightness, adjustable	≈ 5...1000 lx
Brightness measurement range	5 / 1000 Lux

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Connection

Type of connection	with screw terminals
--------------------	----------------------

Settings

Response value sensitivity adjustable	Yes
Delay time, adjustable	5 s...30 mn

Scope of delivery

Component	with fitting material
-----------	-----------------------

Equipment	
Remote controllable	EE806
Angle of horizontal detection	140 °
Slewing	vertically slewing and horizontally rotating
Safety	
Protection index IP	IP55
Use conditions	
Operating temperature	-20...55 °C
Storage/transport temperature	-20...60 °C
Identification	
Application, usage	Motion detector
Main design line	Motion detectors