



EE861



IP55

IP55 Motion Detector Comfort 220° Anthracite

Technical properties

Architecture

Fixing mode surface-mounting

Main electrical features

Frequency 50/60 Hz

Dimensions

Height of installed product 2.5 m

Recommended installation height 2.5 m

Measurement

Detection Method Passive Infrared

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 220 °

Detection angle 220 °

Frontal detecting distance 16 m

Side detecting distance 10 m

Materials

Colour charcoal

RAL colour RAL 7016 - Anthracite grey

Material plastic

Lighting control

Response brightness, adjustable ≈ 5...1000 lx

Brightness measurement range 5 / 1000 Lux

Installation, mounting

Maximum Mounting Height 4 m

Connection

Type of connection with screw terminals

Settings

Response value sensitivity adjustable Yes

Delay time, adjustable 5 s...30 mn

Scope of delivery

Equipment

Remote controllable	EE806
Angle of horizontal detection	220 °
Slewing	vertically slewing and horizontally rotating

Safety

Protection index IP	IP55
---------------------	------

Use conditions

Operating temperature	-20...55 °C
Storage/transport temperature	-20...60 °C

Identification

Application, usage	Motion detector
Main design line	Motion detectors
