




EE870



**IP55 Motion Detector Comfort 220/360° White**

**Technical properties**

**Architecture**

Bus system Without

**Functions**

Function Presence simulation ; can be used as a single unit, main device or extension unit

Operating mode with 2 operating modes: time- and light-dependent switch on or pulse mode

**Main electrical features**

Frequency 50/60 Hz

**Voltage**

Operating voltage 230 V~ +10%/-15%

**Dimensions**

Height of installed product 2.5 m

Length 153 mm

Recommended installation height 2.5 m

**Power**

Power consumption (standby) ≈ 1.2 W

Incandescent bulb power 2300 W

**Measurement**

Detection field, semi-circular shaped ≈ 10 x 20 m

**Reach distance**

Range, side each ≈ 10 m

**Camera**

Lens Lens setting horizontal ± 80° ; Lens setting vertical - 30 ... +90°

**Power supply**

Supply voltage 230 V AC

**Detection**

Detection angle 220 / 360 °

Detection angle 360 °

Detection angle 220 °

Detection field Ø, on floor ≈ 6 m

**Materials**

Colour	white
--------	-------

**Lighting control**

Response brightness, adjustable	≈ 5...1000 lx
---------------------------------	---------------

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

Fluorescent lamps with electronical ballast (EB)	580 W
--	-------

**Fluorescent bulbs control**

Energy-saving lamps	20 x 20 W
---------------------	-----------

Fluorescent lamps parallel compensated	400 W /47 µF
--	--------------

**LED control**

230V LED lamps	20 x 20 W
----------------	-----------

LED	with LED detection and mode indicator
-----	---------------------------------------

**Incandescent bulbs control**

12 V halogen lamps	1500 W
--------------------	--------

230 V incandescent lamps and halogen lamps	2300 W
--	--------

**Installation, mounting**

Maximum Mounting Height	4 m
-------------------------	-----

**Connection**

Connection type	quick connect
-----------------	---------------

Type of contacts	contact floating
------------------	------------------

Type of connection	with screw terminals
--------------------	----------------------

**Cable**

Wire	with cable entry
------	------------------

**Settings**

Response value sensitivity adjustable	Yes
---------------------------------------	-----

Response sensitivity, settable	20...100 %
--------------------------------	------------

Time delayed range	5s to 30 min
--------------------	--------------

Delay time, adjustable	5 s...30 mn
------------------------	-------------

Setting	with potentiometers for fine adjustment of the response brightness, sensitivity and delay time
---------	--

**Scope of delivery**

Component	with fitting material
-----------	-----------------------

**Equipment**

Potential-free	with potential-free contact
----------------	-----------------------------

Slewing	vertically slewing and horizontally rotating
---------	--

**Safety**

Protection class	isol.class II
------------------	---------------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

**Use conditions**

---

Operating temperature	-20...55 °C
-----------------------	-------------

---

Storage/transport temperature	-20...60 °C
-------------------------------	-------------

---

Energy-saving

low intrinsic energy requirement ; energy saving by means of presence and brightness-dependent ON and OFF switching of light

**Identification**

---

Application, usage	Motion detector
--------------------	-----------------

---

Main design line	Motion detectors
------------------	------------------