




EE701



IP55

## Compact twilight switch basic 8A

### Technical properties

#### Configuration

Number of modules	2
-------------------	---

#### Controls and indicators

Presence button	No
-----------------	----

#### Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

#### Voltage

Operating voltage	230 V~ +10%/-15%
-------------------	------------------

#### Electric current

Acceptable current rating with AC1	8 A
------------------------------------	-----

#### Dimensions

Depth of installed product	42.5 mm
Height of installed product	95 mm
Length	80 mm
Width of installed product	42.5 mm

#### Power

Max. power with fluo uncompensated lamps	400 VA
Conventional transformers	750 VA
Electronic transformers	750 W

#### Power supply

Supply voltage	230 V
----------------	-------

#### Detection

Sensor voltage	230 V
----------------	-------

#### Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

#### Lighting control

Brightness measurement range	10 / 30 Lux
Fluorescent lamps with electronical ballast (EB)	8 x 58 W

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	1000 VA
--	---------

Max. power fluo. duo lamp comp. series	400 W
Compact fluorescent lamps	12 x 20 W
Fluorescent lamps uncompensated	1000 W
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	1000 W
230 V incandescent lamps and halogen lamps	1000 W
<b>Installation, mounting</b>	
Mounting type	surface-mounted
Installation mode	for wall and mast assembly ; with pipe clamp for mast fixing ; Installation possible on flush-mounted box
<b>Connection</b>	
Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 4mm <sup>2</sup>
Conductor cross-section	1...4 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1NO
Type of connection	with screw terminals
<b>Settings</b>	
Delay ON	40 s
Delay OFF	120 s
<b>Equipment</b>	
Brightness	On/off brightness value individually adjustable predefined
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Storage/transport temperature	-30...60 °C
<b>Identification</b>	
Main design line	House electronics