



EH071

Analogue time switch weekly cycle 1 channel 1 module

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Functions

Switching cycles	min. 30000
------------------	------------

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	210 / 230 V
------------------------------	-------------

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth of installed product	65 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Width of installed product	18 mm
----------------------------	-------

Power

Total power loss under IN	0.5 W
---------------------------	-------

Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
---	----------------------

Type of connection	with screw
--------------------	------------

Settings

Summer / Winter time change	manual
-----------------------------	--------

Shortest switching time	105 mn
-------------------------	--------

Type of programming	analog
---------------------	--------

Programming cycle	1X7D.
-------------------	-------

Equipment

Number of channels	1
--------------------	---

Supply failure reserve	200 h
------------------------	-------

Switching cycles at cos φ = 0,6	min. 30000
---	------------

Use

Cycle	weekly
-------	--------

Safety

Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------