



EH209



Daily time switch basic without reserve 2 modules

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Functions

Number of function channels	1
Switching cycles	min. 50000

Configuration

Switch mode	change-over contact, usable as NC or NO
Number of modules	2

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Operating voltage	230 V~
-------------------	--------

Electric current

Max. power with cos phi 0.6	4 A
Switching current at cos φ = 0.6	max. 3 A

Dimensions

Depth of installed product	54 mm
Height of installed product	90 mm
Width of installed product	36 mm
Width of rail mounted device (RMD)	2 modules

Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W
Power dissipation per coil	0.5 W

Incandescent bulbs control

Max. power with incandescent lamps	1000 W
230 V incandescent lamps and halogen lamps	max. 1000 W

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Conductor cross-section (flexible)	1...4 mm ²
Conductor cross-section (rigid)	1...4 mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	manual
Shortest switching time	30 mn
Type of programming	analog
Program cycles	Programme cycle: 24 hours
Programming cycle	24H

Equipment

Number of channels	1
Number of switching times for on/off	96
Supply failure reserve	without
Switching cycles at $\cos \varphi = 0,6$	min. 20000

Use

Cycle	daily
-------	-------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...55 °C
Working accuracy	6 mn / year
Storage/transport temperature	-20...70 °C

Identification

Main design line	Light control
------------------	---------------