



EE960

Emergency light

Technical properties

Configuration

Number of modules	3
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Rated voltage	230 V
Frequency	50 Hz

Voltage

Type of input voltage	AC
-----------------------	----

Dimensions

Depth of installed product	51 mm
Height of installed product	70 mm
Length	51 mm
Width of installed product	54 mm

Power

Total power loss under IN	1 W
---------------------------	-----

Battery

Battery recharge time	30 h
-----------------------	------

Power supply

Supply voltage	230 V
----------------	-------

Materials

Material	plastic
----------	---------

Lighting control

Autonomy for a lamp	90 mn
---------------------	-------

Incandescent bulbs control

Max. power with incandescent lamps	1 W
------------------------------------	-----

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	Clamp/screw mounting

Equipment

Number of remote controlling components	0
On/Off switch	No

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	0...40 °C
Storage/transport temperature	-5...60 °C
