



EH716



Time switch 72X72 24H 48VDC 110/230VAC + RES

Technical properties

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage Ue	110 / 230 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	45 mm
Height of installed product	72 mm
Dimensions (LLxwxhxh)	72 x 72 x 48,5
Width of installed product	72 mm

Battery

Charging time of the power reserve in hours	200
---	-----

Incandescent bulbs control

Max. power with incandescent lamps	1000 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1 / 6mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw

Settings

Number of program steps	72
Summer / Winter time change	manual
Shortest switching time	10 mn
Type of programming	analog
Programming cycle	24H
Astro program	No

Equipment

Number of channels	1
Supply failure reserve	120 h

Use

Cycle	daily
-------	-------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-10...50 °C
Working accuracy	6 mn / year
Storage/transport temperature	-10...60 °C