



EMN005

Multifunction stair case time lag switch

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	195 / 230 / 253 V
Frequency	50/60 Hz

Voltage

Command voltage AC	230 V
--------------------	-------

Electric current

Acceptable current rating with AC1	16 A
Quiescent current	100 mA
Rated current	16 A

Dimensions

Depth of installed product	64 mm
Length	64 mm
Width of installed product	17.5 mm

Power

Max. power with fluo uncompensated lamps	3600 VA
Power consumed	1 VA
Total power loss under IN	2 W
Power dissipation per coil	0.25 W

Power supply

Supply voltage	230 V
----------------	-------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	1000 VA
--	---------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²

Connection type	3 and 4 wires
Number of contacts	1
Type of contacts	1NO
Type of connection	with screw
Settings	
Time delayed range	30s / 10min
Equipment	
Pre-warning time	40 s
Use conditions	
Operating temperature	-10...55 °C
Storage/transport temperature	-20...60 °C