



EMN005

## Multifunction stair case time lag switch

### Technical properties

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage Ue	195 / 230 / 253 V
Frequency	50/60 Hz

#### Voltage

Command voltage AC	230 V
--------------------	-------

#### Electric current

Acceptable current rating with AC1	16 A
Quiescent current	100 mA
Rated current	16 A

#### Dimensions

Depth of installed product	64 mm
Length	64 mm
Width of installed product	17.5 mm

#### Power

Max. power with fluo uncompensated lamps	3600 VA
Power consumed	1 VA
Total power loss under IN	2 W
Power dissipation per coil	0.25 W

#### Power supply

Supply voltage	230 V
----------------	-------

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	1000 VA
--	---------

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>

Connection type	3 and 4 wires
Number of contacts	1
Type of contacts	1NO
Type of connection	with screw
<b>Settings</b>	
Time delayed range	30s / 10min
<b>Equipment</b>	
Pre-warning time	40 s
<b>Use conditions</b>	
Operating temperature	-10...55 °C
Storage/transport temperature	-20...60 °C