



EH011



**IP20**

## Time switch daily cycle with reserve

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Functions

Number of function channels	1
Switching cycles	min. 50000
Power reserve	≈ 200 h

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Frequency	50 Hz
-----------	-------

#### Electric current

Max. power with cos phi 0.6	3 A
Switching current at cos φ = 0.6	max. 3 A

#### Dimensions

Depth of installed product	60 mm
Height of installed product	80 mm
Width of installed product	18 mm
Width of rail mounted device (RMD)	1 modules

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W
Power dissipation per coil	0.5 W

#### Battery

Charging time of the power reserve in hours	120
---	-----

#### Fluorescent bulbs control

Compact fluorescent lamps	max. 100 W
---------------------------	------------

#### Incandescent bulbs control

Max. power with incandescent lamps	900 W
230 V incandescent lamps and halogen lamps	max. 900 W

**Installation, mounting**

Mounting type	din-Rail
Installation mode	for mounting on DIN rail

**Connection**

Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 4mm <sup>2</sup>
Conductor cross-section (flexible)	1...4 mm <sup>2</sup>
Conductor cross-section (rigid)	1...4 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals
Type of connection	with screw

**Settings**

Number of program steps	96
Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog
Program cycles	Programme cycle: 24 hours
Programming cycle	24H

**Equipment**

Number of channels	1
Number of switching times for on/off	96
Supply failure reserve	200 h
Switching cycles at $\cos \varphi = 0,6$	min. 20000

**Use**

Cycle	daily
-------	-------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-10...55 °C
Working accuracy	1
Storage/transport temperature	-10...55 °C