



EMN005

Multifunction stair case time lag switch

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	195 / 230 / 253 V
------------------------------	-------------------

Frequency	50/60 Hz
-----------	----------

Voltage

Command voltage AC	230 V
--------------------	-------

Electric current

Acceptable current rating with AC1	16 A
------------------------------------	------

Quiescent current	100 mA
-------------------	--------

Rated current	16 A
---------------	------

Dimensions

Depth of installed product	64 mm
----------------------------	-------

Length	64 mm
--------	-------

Width of installed product	17.5 mm
----------------------------	---------

Power

Max. power with fluo uncompensated lamps	3600 VA
--	---------

Power consumed	1 VA
----------------	------

Total power loss under IN	2 W
---------------------------	-----

Power dissipation per coil	0.25 W
----------------------------	--------

Power supply

Supply voltage	230 V
----------------	-------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	1000 VA
--	---------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Number of contacts	1
Type of contacts	1NO
Equipment	
Pre-warning time	40 s
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-10...55 °C
Storage/transport temperature	-20...60 °C