



EPN503



Latching relay 1NO+1NC 48V

Technical properties

Functions

Max. temporisation	60 s
--------------------	------

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	250 V
------------------------------	-------

Voltage

Rated insulation voltage	250 V
--------------------------	-------

DC control voltage	24 V
--------------------	------

Command voltage AC	48 V
--------------------	------

Electric current

Quiescent current	6 mA
-------------------	------

Rated current	16 A
---------------	------

Dimensions

Depth of installed product	63 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	17.5 mm
----------------------------	---------

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Inrush power absorbed	25 VA
-----------------------	-------

Total power loss under IN	1.2 W
---------------------------	-------

Resistance

Winding resistance	48 Ω
--------------------	------

Endurance

Electrical durability at nominal load in AC21in operating cycles	150000
--	--------

Number of mechanical operations	500000
---------------------------------	--------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	900 VA
--	--------

Incandescent bulbs control

Max. power with incandescent lamps

1800 W

Installation, mounting

Tightening torque	1,6Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
---	----------------------

Connection cross-sect. rigid cable	1,5 / 10mm ²
------------------------------------	-------------------------

Number of contacts	2
--------------------	---

Type of contacts	1NC+1NO
------------------	---------

Equipment

Type of latching relay	electromechanic
------------------------	-----------------

Use

Pulse duration	50 ms
----------------	-------

Standards

Standard text	IEC/EN 60669-2
---------------	----------------

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------

Manual operation possible	Yes
---------------------------	-----