



EH271



## Weekly time switch with reserve with clock hands 2 modules

### Technical properties

#### Functions

Number of function channels	1
Switching cycles	min. 50000
Slide switch	with slide switch for permanent on/automatic
Power reserve	≈ 200 h

#### Configuration

Switch mode	change-over contact, usable as NC or NO
Number of modules	2

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Operating voltage	230 V~
-------------------	--------

#### Electric current

Max. power with cos phi 0.6	3 A
Switching current at cos φ = 0.6	max. 3 A

#### Dimensions

Depth of installed product	58 mm
Height of installed product	90 mm
Width of installed product	36 mm
Width of rail mounted device (RMD)	2 modules

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W
Power dissipation per coil	0.5 W

#### Measurement

Running accuracy	± 1 s/day
------------------	-----------

#### Battery

Battery / storage battery	with integrated storage battery for power reserve
Charging time of the power reserve in hours	120

#### Incandescent bulbs control

Max. power with incandescent lamps

1000 W

230 V incandescent lamps and halogen lamps

max. 1000 W

### Installation, mounting

Mounting type	din-Rail
Installation mode	for mounting on DIN rail

### Connection

Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 4mm <sup>2</sup>
Conductor cross-section (flexible)	1...4 mm <sup>2</sup>
Conductor cross-section (rigid)	1...4 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals
Contact	with potential-free switching contact
Type of connection	with screw

### Settings

Number of program steps	84
Summer / Winter time change	manual
Shortest switching time	3.5 h
Type of programming	analog
Program cycles	Programme cycles: 1 x 7 days
Programming cycle	1X7D.
Setting	Fine setting of time via rotating hand
Astro program	No

### Equipment

Number of channels	1
Number of switching times for on/off	84
Supply failure reserve	200 h
Switching cycles at $\cos \varphi = 0,6$	min. 20000

### Use

Cycle	weekly
-------	--------

### Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

### Use conditions

Operating temperature	-10...55 °C
Working accuracy	6 mn / year
Storage/transport temperature	-10...55 °C

### Identification

Main design line	Light control
------------------	---------------