



EPN541



Latching relay 4NO 24V

Technical properties

Functions

Max. temporisation	60 s
--------------------	------

Configuration

Number of modules	2
-------------------	---

Main electrical features

Rated operational voltage Ue	250 / 400 V
------------------------------	-------------

Frequency	50/60 Hz
-----------	----------

Voltage

Rated insulation voltage	400 V
--------------------------	-------

DC control voltage	12 V
--------------------	------

Command voltage AC	24 V
--------------------	------

Electric current

Quiescent current	6 mA
-------------------	------

Rated current	16 A
---------------	------

Dimensions

Depth of installed product	63 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	35 mm
----------------------------	-------

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Inrush power absorbed	55 VA
-----------------------	-------

Total power loss under IN	4.8 W
---------------------------	-------

Resistance

Winding resistance	6.4 Ω
--------------------	-------

Endurance

Electrical durability at nominal load in AC21in operating cycles	150000
--	--------

Number of mechanical operations	500000
---------------------------------	--------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	900 VA
--	--------

Incandescent bulbs control

Max. power with incandescent lamps	1800 W
------------------------------------	--------

Installation, mounting

Tightening torque	1,6Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
---	----------------------

Connection cross-sect. rigid cable	1,5 / 10mm ²
------------------------------------	-------------------------

Number of contacts	4
--------------------	---

Type of contacts	4NO
------------------	-----

Type of connection	with screw
--------------------	------------

Equipment

Type of latching relay	electromechanic
------------------------	-----------------

Use

Pulse duration	50 ms
----------------	-------

Standards

Standard text	IEC/EN 60669-2
---------------	----------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------

Manual operation possible	Yes
---------------------------	-----