



EH711



IP20

## Time switch 72X72 24H + reserve

### Technical properties

#### Architecture

Fixing mode surface-mounting

#### Functions

Number of function channels	1
Switching cycles	min. 50000
Power reserve	≈ 120 h

#### Configuration

Switch mode	change-over contact, usable as NC or NO
Number of modules	4

#### Controls and indicators

Manual selection switches / push-buttons as rotary switch for temporary on/off switching

#### Main electrical features

Rated operational voltage U <sub>e</sub>	196 / 230 / 253 V
Frequency	50 Hz

#### Voltage

Operating voltage 230 V~

#### Electric current

Switching current at  $\cos \varphi = 0.6$  max. 3 A

#### Dimensions

Depth of installed product	48.5 mm
Height of installed product	72 mm
Dimensions (LLxwxhh)	72 x 72 x 48,5
Width of installed product	72 mm
Width of rail mounted device (RMD)	4 modules

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W

#### Measurement

Running accuracy ± 1 s/day

**Battery**

Battery / storage battery	with integrated storage battery for power reserve
Charging time of the power reserve in hours	120

**Incandescent bulbs control**

Max. power with incandescent lamps	1000 W
230 V incandescent lamps and halogen lamps	max. 1000 W

**Installation, mounting**

Installation mode	for surface mounting
-------------------	----------------------

**Connection**

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 6mm <sup>2</sup>
Conductor cross-section (flexible)	1...6 mm <sup>2</sup>
Conductor cross-section (rigid)	1...6 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals
Contact	with potential-free switching contact
Type of connection	with screw

**Settings**

Number of program steps	72
Summer / Winter time change	manual
Shortest switching time	10 mn
Type of programming	analog
Program cycles	Programme cycle: 24 hours
Programming cycle	24H
Setting	Setting via day dial

**Equipment**

Number of channels	1
Number of switching times for on/off	72
Supply failure reserve	200 h
Switching cycles at $\cos \varphi = 0,6$	min. 20000

**Use**

Cycle	daily
-------	-------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-10...50 °C
Working accuracy	1
Storage/transport temperature	-20...60 °C

**Identification**

