



EH716



## Time switch 72X72 24H 48VDC 110/230VAC + RES

### Technical properties

#### Configuration

Number of modules	4
-------------------	---

#### Main electrical features

Rated operational voltage Ue	110 / 230 V
Frequency	50/60 Hz

#### Dimensions

Depth of installed product	45 mm
Height of installed product	72 mm
Dimensions (LLxwxh)	72 x 72 x 48,5
Width of installed product	72 mm

#### Battery

Charging time of the power reserve in hours	200
---	-----

#### Incandescent bulbs control

Max. power with incandescent lamps	1000 W
------------------------------------	--------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 6mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw

#### Settings

Number of program steps	72
Summer / Winter time change	manual
Shortest switching time	10 mn
Type of programming	analog
Programming cycle	24H
Astro program	No

#### Equipment

Number of channels	1
Supply failure reserve	120 h

#### Use

Cycle	daily
-------	-------

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-10...50 °C
Working accuracy	6 mn / year
Storage/transport temperature	-10...60 °C