



EH770

Weekly time switch 1 channel, analog, 72x72

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Main electrical features

| | |
|------------------------------|-------------------|
| Rated operational voltage Ue | 196 / 230 / 253 V |
| Frequency | 50 Hz |

Dimensions

| | |
|-----------------------------|----------------|
| Depth of installed product | 48.5 mm |
| Height of installed product | 72 mm |
| Dimensions (LLxwxhxh) | 72 x 72 x 48,5 |
| Width of installed product | 72 mm |

Incandescent bulbs control

| | |
|------------------------------------|--------|
| Max. power with incandescent lamps | 1000 W |
|------------------------------------|--------|

Connection

| | |
|---|----------------------|
| Connection cross-sect. flexible conductor | 1 / 6mm ² |
| Connection cross-sect. rigid cable | 1 / 6mm ² |
| Number of contacts | 1 |
| Type of contacts | 1 changeover |
| Type of connection | with screw |

Settings

| | |
|-----------------------------|--------|
| Number of program steps | 84 |
| Summer / Winter time change | manual |
| Shortest switching time | 60 mn |
| Type of programming | analog |
| Programming cycle | 1X7D. |
| Astro program | No |

Equipment

| | |
|------------------------|---------|
| Number of channels | 1 |
| Supply failure reserve | without |

Use

| | |
|-------|--------|
| Cycle | weekly |
|-------|--------|

Safety

| | |
|---------------|-----|
| REACH conform | No |
| RoHS conform | Yes |

Halogen free

No

Use conditions

Operating temperature

-10...50 °C

Working accuracy

1

Storage/transport temperature

-20...60 °C