



ERD217

Relay 16A, 2NC, 24V~50Hz

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	250 V
DC control voltage	0 V
Command voltage AC	24 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	16 A
Thermal rated current outside of housings	16 A
Acceptable current load with AC7 category A	16 A
Acceptable current load with AC7 category B	5.5 A

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

Power

Inrush power absorbed	10.7 VA
Operating consumption	2.9 VA
Total power loss under IN	2 W
Power loss per contact	1 W
Power dissipation per coil	1 W
Contact rating with 230 V in AC7 category A	3 kW
Contact rating with 230 V in AC7 category B	880 W

Tripping

Time of response when opening	15 ms
Time of response when closing	25 ms

Endurance

Electric endurance in number of cycles	30000
--	-------

Number of mechanical operations	100000
Fluorescent bulbs control	
Max. power with fluorescent parallel lamps	490 VA
Fluorescent lamps in duo circuit	1200 VA
Max. load fluorescent lamp	570 VA
Incandescent bulbs control	
Max. power with incandescent lamps	1100 W
Connection	
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-section of the control cable solid	1 / 10 mm ²
Equipment	
Quantity of NC contacts	2
Quantity of NO contacts	0
Can be accessorized	Yes
Use	
Local operation/hand operation	Yes
Standards	
European directive WEEE	concerned
Safety	
Protection index IP	IP2X
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C