



ESC227

Contactor 25A, 1NO+1NC, 230V~50Hz

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	250 V
DC control voltage	0 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	25 A
Thermal rated current outside of housings	25 A
Acceptable current load with AC7 category A	25 A
Acceptable current load with AC7 category B	8.5 A

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

Power

Inrush power absorbed	10.7 VA
Operating consumption	2.9 VA
Total power loss under IN	2.5 W
Power loss per contact	1.5 W
Power dissipation per coil	1 W
Contact rating with 230 V in AC7 category A	4.6 kW
Contact rating with 230 V in AC7 category B	880 W

Tripping

Time of response when opening	15 ms
Time of response when closing	25 ms

Endurance

Electric endurance in number of cycles	30000
----------------------------------------	-------

Number of mechanical operations 100000

Fluorescent bulbs control

Max. power with fluorescent parallel lamps 810 VA

Fluorescent lamps in duo circuit 1990 VA

Max. load fluorescent lamp 950 VA

Incandescent bulbs control

Max. power with incandescent lamps 1900 W

Connection

Connection cross-section of the control cable solid 1 / 10 mm²

Equipment

Can be accessorized Yes

Use

Local operation/hand operation No

Standards

European directive WEEE concerned

Safety

Protection index IP IP2X

Use conditions

Operating temperature -10...50 °C

Storage/transport temperature -40...80 °C