



ESC080

## Auxiliary contact 6A, 1NO+1NC

### Technical properties

#### Configuration

Number of modules	0.5
-------------------	-----

#### Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

#### Voltage

Rated insulation voltage	240 V
Rated impulse withstand voltage	4 kV

#### Electric current

Acceptable current rating with AC1	6 A
Rated current	6 A

#### Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	11 mm

#### Power

Total power loss under IN	0.1 W
---------------------------	-------

#### Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

#### Connection

Number of contacts	2
Connection cross-section of the control cable solid	1 / 10 mm <sup>2</sup>

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------

