



ESC080

Auxiliary contact 6A, 1NO+1NC

Technical properties

Configuration

Number of modules	0.5
-------------------	-----

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Voltage

Rated insulation voltage	240 V
--------------------------	-------

Rated impulse withstand voltage	4 kV
---------------------------------	------

Electric current

Acceptable current rating with AC1	6 A
------------------------------------	-----

Rated current	6 A
---------------	-----

Dimensions

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	11 mm
----------------------------	-------

Power

Total power loss under IN	0.1 W
---------------------------	-------

Endurance

Electric endurance in number of cycles	30000
--	-------

Number of mechanical operations	1000000
---------------------------------	---------

Connection

Number of contacts	2
--------------------	---

Connection cross-section of the control cable solid	1 / 10 mm ²
---	------------------------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------