



ESC466

Contactor 63A, 3NO+1NC, 230V~50Hz

Technical properties

Architecture

Type of order	Not applicable
Number of poles	4 P

Configuration

Number of modules	3
-------------------	---

Main electrical features

Rated operational voltage Ue	400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	440 V
DC control voltage	0 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	63 A
Thermal rated current outside of housings	63 A
Acceptable current load with AC7 category A	63 A
Acceptable current load with AC7 category B	32 A

Dimensions

Depth of installed product	60 mm
Height of installed product	85 mm
Width of installed product	54 mm

Power

Inrush power absorbed	62.5 VA
Operating consumption	5.7 VA
Total power loss under IN	16.5 W
Power loss per contact	5 W
Power dissipation per coil	1.5 W
Contact rating with 230 V in AC7 category A	11.6 kW
Contact rating with 230 V in AC7 category B	3.3 kW
Contact rating with 400 V in AC7 category A	35 kW
Contact rating with 400 V in AC7 category B	10 kW

Tripping	
Time of response when opening	20 ms
Time of response when closing	25 ms
Resistance	
Winding resistance	770 Ω
Endurance	
Electric endurance in number of cycles	30000
Number of mechanical operations	100000
Fluorescent bulbs control	
Max. power with fluorescent parallel lamps	2100 VA
Fluorescent lamps in duo circuit	4700 VA
Max. load fluorescent lamp	3000 VA
Incandescent bulbs control	
Max. power with incandescent lamps	6500 W
Installation, mounting	
Tightening torque	Coil: 2,5Nm ; Power: 3,5Nm
Connection	
Connection cross-sect. flexible conductor	1,5 / 16mm ²
Connection cross-sect. rigid cable	1,5 / 25mm ²
Number of contacts	4
Type of contacts	3NO+1NC
Type of connection	with screw
Connection cross-section of the control cable solid	1 / 2.5 mm ²
Equipment	
Can be accessorized	Yes
Use	
Local operation/hand operation	No
Safety	
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C