



ESD225

**Contactor 25A, 2NO, 24V~50Hz**

**Technical properties**

**Architecture**

Type of order	Not applicable
---------------	----------------

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	250 V
DC control voltage	0 V
Command voltage AC	24 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	25 A
Thermal rated current outside of housings	25 A
Acceptable current load with AC7 category A	25 A
Acceptable current load with AC7 category B	8.5 A

**Dimensions**

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

**Power**

Inrush power absorbed	10.7 VA
Operating consumption	2.9 VA
Total power loss under IN	4 W
Power loss per contact	1.5 W
Power dissipation per coil	1 W
Contact rating with 230 V in AC7 category A	4.6 kW
Contact rating with 230 V in AC7 category B	880 W

**Tripping**

Time of response when opening	15 ms
Time of response when closing	25 ms

**Endurance**

Electric endurance in number of cycles	30000
Number of mechanical operations	100000

**Fluorescent bulbs control**

Max. power with fluorescent parallel lamps	810 VA
Fluorescent lamps in duo circuit	1990 VA
Max. load fluorescent lamp	950 VA

**Incandescent bulbs control**

Max. power with incandescent lamps	1900 W
------------------------------------	--------

**Installation, mounting**

Tightening torque	1,2Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 10mm <sup>2</sup>
Type of contacts	2NO
Type of connection	with screw
Connection cross-section of the control cable solid	1 / 10 mm <sup>2</sup>

**Equipment**

Can be accessorized	Yes
---------------------	-----

**Use**

Local operation/hand operation	No
--------------------------------	----

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C