



ESC227

Contactor 25A, 1NO+1NC, 230V~50Hz

Technical properties

Architecture

| | |
|---------------|----------------|
| Type of order | Not applicable |
|---------------|----------------|

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|---------------------------------|-------|
| Rated operational voltage U_e | 230 V |
| Frequency | 50 Hz |

Voltage

| | |
|---------------------------------|-------|
| Rated insulation voltage | 250 V |
| DC control voltage | 0 V |
| Command voltage AC | 230 V |
| Rated impulse withstand voltage | 4 kV |

Electric current

| | |
|---|-------|
| Rated current | 25 A |
| Thermal rated current outside of housings | 25 A |
| Acceptable current load with AC7 category A | 25 A |
| Acceptable current load with AC7 category B | 8.5 A |

Dimensions

| | |
|-----------------------------|----------|
| Depth of installed product | 60 mm |
| Height of installed product | 83 mm |
| Width of installed product | 17.85 mm |

Power

| | |
|---|---------|
| Inrush power absorbed | 10.7 VA |
| Operating consumption | 2.9 VA |
| Total power loss under IN | 2.5 W |
| Power loss per contact | 1.5 W |
| Power dissipation per coil | 1 W |
| Contact rating with 230 V in AC7 category A | 4.6 kW |
| Contact rating with 230 V in AC7 category B | 880 W |

Tripping

| | |
|-------------------------------|-------|
| Time of response when opening | 15 ms |
| Time of response when closing | 25 ms |

Endurance

| | |
|--|--------|
| Electric endurance in number of cycles | 30000 |
| Number of mechanical operations | 100000 |

Fluorescent bulbs control

| | |
|--|---------|
| Max. power with fluorescent parallel lamps | 810 VA |
| Fluorescent lamps in duo circuit | 1990 VA |
| Max. load fluorescent lamp | 950 VA |

Incandescent bulbs control

| | |
|------------------------------------|--------|
| Max. power with incandescent lamps | 1900 W |
|------------------------------------|--------|

Installation, mounting

| | |
|-------------------|-------|
| Tightening torque | 1,2Nm |
|-------------------|-------|

Connection

| | |
|---|------------------------|
| Connection cross-sect. flexible conductor | 1 / 6mm ² |
| Connection cross-sect. rigid cable | 1 / 10mm ² |
| Type of contacts | 1NC+1NO |
| Type of connection | with screw |
| Connection cross-section of the control cable solid | 1 / 10 mm ² |

Equipment

| | |
|---------------------|-----|
| Can be accessorized | Yes |
|---------------------|-----|

Use

| | |
|--------------------------------|----|
| Local operation/hand operation | No |
|--------------------------------|----|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...50 °C |
| Storage/transport temperature | -40...80 °C |