



ESD125S

Humfree Contactor 25A, 1NO, 24V~ 50Hz & 24V DC

Technical properties

Architecture

Type of order	Not applicable
---------------	----------------

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	250 V
DC control voltage	0 V
Command voltage AC	24 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	25 A
Thermal rated current outside of housings	25 A
Acceptable current load with AC7 category A	25 A
Acceptable current load with AC7 category B	8.5 A

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

Power

Inrush power absorbed	2.4 VA
Operating consumption	2.2 VA
Total power loss under IN	3.7 W
Power loss per contact	1.5 W
Power dissipation per coil	2.2 W
Contact rating with 230 V in AC7 category A	4.6 kW
Contact rating with 230 V in AC7 category B	880 W

Tripping

Time of response when opening	15 ms
Time of response when closing	25 ms

Endurance	
Electric endurance in number of cycles	30000
Number of mechanical operations	100000
Fluorescent bulbs control	
Max. power with fluorescent parallel lamps	810 VA
Fluorescent lamps in duo circuit	1990 VA
Max. load fluorescent lamp	950 VA
Incandescent bulbs control	
Max. power with incandescent lamps	1900 W
Installation, mounting	
Tightening torque	1,2Nm
Connection	
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1 / 10mm ²
Type of contacts	1NO
Type of connection	with screw
Connection cross-section of the control cable solid	1 / 10 mm ²
Equipment	
Can be accessorized	No
Use	
Local operation/hand operation	No
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C