



ESD264

Contactor 63A, 2NC, 24V~50Hz

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 2 P |
|-----------------|-----|

Configuration

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 400 V |
|------------------------------|-------|

| | |
|-----------|-------|
| Frequency | 50 Hz |
|-----------|-------|

Voltage

| | |
|--------------------------|-------|
| Rated insulation voltage | 440 V |
|--------------------------|-------|

| | |
|--------------------|-----|
| DC control voltage | 0 V |
|--------------------|-----|

| | |
|--------------------|------|
| Command voltage AC | 24 V |
|--------------------|------|

| | |
|---------------------------------|------|
| Rated impulse withstand voltage | 4 kV |
|---------------------------------|------|

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

| | |
|---|------|
| Thermal rated current outside of housings | 63 A |
|---|------|

| | |
|---|------|
| Acceptable current load with AC7 category A | 63 A |
|---|------|

| | |
|---|------|
| Acceptable current load with AC7 category B | 32 A |
|---|------|

Dimensions

| | |
|----------------------------|-------|
| Depth of installed product | 60 mm |
|----------------------------|-------|

| | |
|-----------------------------|-------|
| Height of installed product | 85 mm |
|-----------------------------|-------|

| | |
|----------------------------|-------|
| Width of installed product | 54 mm |
|----------------------------|-------|

Power

| | |
|-----------------------|-------|
| Inrush power absorbed | 60 VA |
|-----------------------|-------|

| | |
|-----------------------|------|
| Operating consumption | 7 VA |
|-----------------------|------|

| | |
|---------------------------|------|
| Total power loss under IN | 10 W |
|---------------------------|------|

| | |
|------------------------|-----|
| Power loss per contact | 5 W |
|------------------------|-----|

| | |
|----------------------------|-------|
| Power dissipation per coil | 2.2 W |
|----------------------------|-------|

| | |
|---|---------|
| Contact rating with 230 V in AC7 category A | 11.6 kW |
|---|---------|

| | |
|---|--------|
| Contact rating with 230 V in AC7 category B | 3.3 kW |
|---|--------|

| | |
|---|-------|
| Contact rating with 400 V in AC7 category A | 35 kW |
|---|-------|

| | |
|---|--------|
| Contact rating with 400 V in AC7 category B | 7.8 kW |
|---|--------|

Tripping

| | |
|---|-------------------------|
| Time of response when opening | 20 ms |
| Time of response when closing | 25 ms |
| Resistance | |
| Winding resistance | 5.6 Ω |
| Endurance | |
| Electric endurance in number of cycles | 30000 |
| Number of mechanical operations | 1000000 |
| Fluorescent bulbs control | |
| Max. power with fluorescent parallel lamps | 2100 VA |
| Fluorescent lamps in duo circuit | 4700 VA |
| Max. load fluorescent lamp | 3000 VA |
| Incandescent bulbs control | |
| Max. power with incandescent lamps | 6500 W |
| Connection | |
| Number of contacts | 2 |
| Connection cross-section of the control cable solid | 1 / 2.5 mm ² |
| Equipment | |
| Can be accessorized | Yes |
| Use | |
| Local operation/hand operation | No |
| Standards | |
| European directive WEEE | concerned |
| Safety | |
| Protection index IP | IP2X |
| Protection class | isol.class II |
| Use conditions | |
| Operating temperature | -10...50 °C |
| Storage/transport temperature | -40...80 °C |