



EU102

## control relay monophased voltage 230V

### Technical properties

#### Architecture

|             |          |
|-------------|----------|
| Fixing mode | Din-Rail |
|-------------|----------|

#### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

#### Main electrical features

|           |          |
|-----------|----------|
| Frequency | 50/60 Hz |
|-----------|----------|

#### Electric current

|                                    |     |
|------------------------------------|-----|
| Acceptable current rating with AC1 | 8 A |
|------------------------------------|-----|

#### Dimensions

|        |       |
|--------|-------|
| Length | 64 mm |
|--------|-------|

#### Power

|                           |     |
|---------------------------|-----|
| Total power loss under IN | 4 W |
|---------------------------|-----|

#### Measurement

|                           |             |
|---------------------------|-------------|
| Voltage measurement range | 15 to 480 V |
|---------------------------|-------------|

#### Installation, mounting

|               |          |
|---------------|----------|
| Mounting type | din-Rail |
|---------------|----------|

#### Connection

|   |                      |
|---|----------------------|
| Connection cross-sect. flexible conductor | 1 / 6mm <sup>2</sup> |
| Type of contacts                          | 1 changeover         |

#### Settings

|           |        |
|-----------|--------|
| Delay OFF | 1200 s |
|-----------|--------|

#### Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP30 |
|---------------------|------|

#### Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -20...55 °C |
| Storage/transport temperature | -40...70 °C |