



EV106

IP20

## Remote control dimmer 1-10V

### Technical properties

#### Architecture

Type of order 1-10V

#### Configuration

Number of modules 4

#### Controls and indicators

Indication / display with 2-digit, 7-segment function channel display

Button / push-button with actuation button for switching on/off ; with 2 actuation buttons for dimming up/down

#### Connectivity

Outputs switching output for disconnection of connected electronic ballasts

Maximum connection distance to the priority inputs 50 m

Interface with 1-10 V interface

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50 Hz

#### Voltage

Operating voltage 230 V

Operating voltage 230 V $\sim$  +/- 10%

#### Electric current

Control current 1-10 V (master) 50 mA

Control current 1-10 V (slave) 50 mA

Rated current 10 A

#### Dimensions

Depth of installed product 65 mm

Height of installed product 85 mm

Installation height 0 / 1000 m

Length 65 mm

Width of installed product 71 mm

Width of rail mounted device (RMD) 4 modules

#### Length

Max distance to switches 50 mm

Max. Distance of connection 1-10V 50 m

<b>Power</b>	
Power consumed	3 W
Power consumption (operation)	3 W
Power consumption (standby)	1 W
Total power loss under IN	1 W
Power dissipation per coil	1.3 W

#### **Cover, door**

Surface cover	Other
---------------	-------

#### **Detection**

Sensor insulation class	class I
-------------------------	---------

#### **Materials**

RAL colour	RAL 7035 - Light grey
Surface appearance	matt

#### **Installation, mounting**

Fixing type	With claws
Mounting type	din-Rail
Installation mode	for mounting on DIN rail

#### **Connection**

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of load	1-10 V
Conductor cross-section (flexible)	1...16 mm <sup>2</sup>
Conductor cross-section (rigid)	1.5...10 mm <sup>2</sup>
Type of connection	with screw terminals
Connection	Connection for illuminated (max. 5 mA) or standard push-buttons
Type of connection	with screw

#### **Settings**

Setting	Brightness limit and dimming speed adjustable via display
---------	---

#### **Equipment**

Switching contact potential-free	16 A, 230 V~ AC1
----------------------------------	------------------

#### **Standards**

Approvals	CE
-----------	----

#### **Safety**

REACH conform	No
Halogen free	No

#### **Use conditions**

Operating temperature	-10...45 °C
Storage/transport temperature	-20...60 °C

#### **Identification**

Subject to technical modifications

---

Composition	basis element
Device family	EV
Main design line	House electronics

---