




EVN002



IP20

Remote Control Dimmer universal 500W

Technical properties

Architecture

Type of order Push button

Configuration

Number of modules 2

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Voltage

Operating voltage 230 V~ +10%/-15%

Fuse

Fuse with electronic short-circuit and overload protection

Dimensions

Depth of installed product 62 mm

Height of installed product 85 mm

Installation height 0 / 1000 m

Width of installed product 35 mm

Width of rail mounted device (RMD) 2 modules

Length

Max distance to switches 50 mm

Power

Dimmable conventional transformers 500 VA

Halogen switching capacity 230V 500 W

Power consumed 4.5 W

Power consumption (operation) 4.5 W

Power consumption (standby) 0.2 W

Incandescent bulb power 500 W

Total power loss under IN 0.2 W

Conventional transformers 500 VA

Electronic transformers 500 W

Cover, door

Surface cover Other

Materials

Surface appearance

matt

Fluorescent bulbs control

| | |
|--|-------|
| Dimmable energy-saving lamps | 100 W |
| Lighting power fluocompact lamps with built-in ballast | 100 W |

LED control

| | |
|--|-------|
| Quantity of dimmable, 230 V retrofit LED lamps | 10 |
| Max number of LED/CFL lamps | 10 |
| Dimmable 230 V LED lamps | 100 W |
| Power LED | 100 W |

Incandescent bulbs control

| | |
|--|-------|
| Max. power with incandescent lamps | 500 W |
| 230 V incandescent lamps and halogen lamps | 500 W |

Installation, mounting

| | |
|-------------------|--------------------------|
| Fixing type | With claws |
| Mounting type | din-Rail |
| Installation mode | for mounting on DIN rail |

Connection

| | |
|---|---|
| Connection cross-sect. flexible conductor | 1,5 / 6mm ² |
| Connection cross-sect. rigid cable | 1,5 / 6mm ² |
| Type of load | universal |
| Conductor cross-section (flexible) | 1.5...6 mm ² |
| Conductor cross-section (rigid) | 1.5...6 mm ² |
| Type of connection | with screw terminals |
| Connection | Connection for non-illuminated push-buttons |
| Type of connection | with screw |

Cable

| | |
|-------------------|------|
| Load cable length | 50 m |
|-------------------|------|

Equipment

| | |
|-------------------|--------------------------|
| Type of dimmer | No |
| Dimming principle | automatic load detection |

Safety

| | |
|---------------|-----|
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -20...50 °C |
| Storage/transport temperature | -20...50 °C |

Instructions

| | |
|------------------|-----------------------------------|
| Information text | Only for use with dimmable lamps! |
|------------------|-----------------------------------|