



EZN001



## Delay on Timer

### Technical properties

#### Architecture

Fixing mode Din-Rail

#### Functions

Switching cycles min. 50000

#### Configuration

Switch mode change-over contact, usable as NC or NO

Number of modules 1

#### Main electrical features

Rated operational voltage  $U_e$  12 / 230 V

Frequency 50/60 Hz

#### Electric current

Max. power with  $\cos \phi$  0.6 5 A

Switching current at  $\cos \phi = 0.6$  max. 5 A

#### Dimensions

Depth of installed product 58 mm

Height of installed product 85 mm

Length 64 mm

Width of installed product 17.5 mm

Width of rail mounted device (RMD) 1 modules

#### Power

Power consumed 15 VA

Power consumption (operation) 15 VA

Total power loss under IN 2 W

Loss power at full load  $\approx$  2 W

Power dissipation per coil 0.5 W

#### Incandescent bulbs control

Max. power with incandescent lamps 450 W

230 V incandescent lamps and halogen lamps max. 450 W

#### Installation, mounting

Mounting type din-Rail

Installation mode for mounting on DIN rail

**Connection**

Conductor cross-section (flexible)	1...6 mm <sup>2</sup>
Conductor cross-section (rigid)	1.5...10 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

**Settings**

Delay time, adjustable	0.1 s...10 h
------------------------	--------------

**Use conditions**

Operating temperature	-10...50 °C
Storage/transport temperature	-40...70 °C

**Instructions**

Special note text	Notice: Not suitable for connection to safety extra-low voltage (SELV).
-------------------	---