



EVN011



**IP20**

## Remote Control Dimmer universal 300W

### Technical properties

#### Architecture

Type of order	Push button
Fixing mode	Din-Rail

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Voltage

Operating voltage	230 V~ +10%/-15%
-------------------	------------------

#### Fuse

Fuse	with electronic short-circuit and overload protection
------	---

#### Dimensions

Depth of installed product	65 mm
Height of installed product	90 mm
Installation height	0 / 1000 m
Width of installed product	17.5 mm
Width of rail mounted device (RMD)	1 modules

#### Length

Max distance to switches	50 mm
--------------------------	-------

#### Power

Dimmable conventional transformers	300 VA
Halogen switching capacity 230V	300 W
Power consumed	2.1 W
Power consumption (operation)	2.1 W
Incandescent bulb power	300 W
Total power loss under IN	0.2 W
Conventional transformers	300 VA
Electronic transformers	300 W

#### Cover, door

Surface cover	Other
---------------	-------

#### Materials

RAL colour	
Surface appearance	matt

### Fluorescent bulbs control

Dimmable energy-saving lamps	60 W
Lighting power fluocompact lamps with built-in ballast	60 W

### LED control

Quantity of dimmable, 230 V retrofit LED lamps	8
Max number of LED/CFL lamps	8
Dimmable 230 V LED lamps	60 W
Power LED	60 W

### Incandescent bulbs control

Max. power with incandescent lamps	300 W
230 V incandescent lamps and halogen lamps	300 W

### Installation, mounting

Fixing type	With claws
Mounting type	din-Rail
Installation mode	for mounting on DIN rail

### Connection

Connection cross-sect. flexible conductor	1,5 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 6mm <sup>2</sup>
Type of load	universal
Conductor cross-section (flexible)	1.5...6 mm <sup>2</sup>
Conductor cross-section (rigid)	1.5...6 mm <sup>2</sup>
Type of connection	with screw terminals
Type of connection	with screw

### Cable

Load cable length	50 m
-------------------	------

### Equipment

Type of dimmer	No
Dimming principle	automatic load detection

### Safety

Protection index IP	IP20
---------------------	------

### Use conditions

Operating temperature	-10...45 °C
Storage/transport temperature	-25...70 °C

### Instructions

Information text	Only for use with dimmable lamps!
------------------	-----------------------------------