



EZN002



IP40



Delay off Timer

Technical properties

Architecture

Fixing mode Din-Rail

Functions

Switching cycles min. 50000

Configuration

Switch mode change-over contact, usable as NC or NO

Number of modules 1

Main electrical features

Rated operational voltage U_e 12 / 230 V

Frequency 50/60 Hz

Electric current

Max. power with $\cos \phi$ 0.6 5 A

Switching current at $\cos \phi = 0.6$ max. 5 A

Dimensions

Depth of installed product 58 mm

Height of installed product 85 mm

Length 64 mm

Width of installed product 17.5 mm

Width of rail mounted device (RMD) 1 modules

Power

Power consumed 15 VA

Power consumption (operation) 15 VA

Total power loss under IN 2 W

Loss power at full load \approx 2 W

Power dissipation per coil 0.5 W

Incandescent bulbs control

Max. power with incandescent lamps 450 W

230 V incandescent lamps and halogen lamps max. 450 W

Installation, mounting

Mounting type din-Rail

Installation mode for mounting on DIN rail

Connection

Conductor cross-section (flexible)	1...6 mm ²
Conductor cross-section (rigid)	1.5...10 mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Delay ON	0.1 s
Delay time, adjustable	0.1 s...10 h
Delay OFF	0.1 s

Use conditions

Operating temperature	-10...50 °C
Storage/transport temperature	-40...70 °C

Instructions

Special note text	Notice: Not suitable for connection to safety extra-low voltage (SELV).
-------------------	---