



FL213B

Polyester enclosure, Orion.Plus, plain door 500x400x200 mm

Technical properties

Functions

| | |
|---------------------------------|----|
| Cover with overpressure release | No |
|---------------------------------|----|

Configuration

| | |
|-------------------|----|
| Number of modules | 54 |
|-------------------|----|

Compatibility

| | |
|-----------------------------------|----|
| Suitable for lightning protection | No |
|-----------------------------------|----|

Electric current

| | |
|---------------|-------|
| Rated current | 630 A |
|---------------|-------|

Dimensions

| | |
|--------------------------------|--------|
| Depth of installed product | 200 mm |
| Internal depth | 200 mm |
| Height of installed product | 500 mm |
| Width of installed product | 400 mm |
| Width in division units | 18 |
| Thickness of sidewall material | 2 mm |

Cover, door

| | |
|-------------------------------|----------------|
| Interlockable | Yes |
| Number of keylock of the door | 2 |
| Cover type | Closed (plain) |
| Door leave | single |
| Cover type | Door |
| Transparent cover or door | No |

Materials

| | |
|---------------------------|-----------------------|
| Colour | light grey |
| RAL colour | RAL 7035 - Light grey |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|--------------------------|-----|
| Suitable for outdoor use | Yes |
|--------------------------|-----|

Settings

| | |
|----------------|--------------|
| Enclosure type | Wall cabinet |
|----------------|--------------|

Equipment

| | |
|----------------|---|
| Number of rows | 3 |
|----------------|---|

| | |
|--------------------------------------|---|
| Number of keys | 2 |
| Quantity of rails | 3 |
| Number of openings for flange plates | 0 |

Standards

| | |
|-----------|-------------|
| Approvals | BS EN 62208 |
|-----------|-------------|

Safety

| | |
|---|---------------|
| IK protection code against mechanical impacts | IK10 |
| Protection class | isol.class II |
| REACH conform | No |
| RoHS conform | Yes |