



FM218

**Floor standing steel enclosure, Quadro5, 1860x700x400 mm**

**Technical properties**

**Configuration**

|                   |     |
|-------------------|-----|
| Number of modules | 264 |
|-------------------|-----|

**Compatibility**

|                                   |    |
|-----------------------------------|----|
| Suitable for lightning protection | No |
|-----------------------------------|----|

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 630 A |
|---------------|-------|

**Dimensions**

|                                |         |
|--------------------------------|---------|
| Insertion depth                | 400 mm  |
| Depth of installed product     | 400 mm  |
| Internal depth                 | 400 mm  |
| Height of installed product    | 1860 mm |
| Width of installed product     | 700 mm  |
| Width in division units        | 24      |
| Thickness of sidewall material | 1.2 mm  |

**Cover, door**

|                           |                |
|---------------------------|----------------|
| Material thickness cover  | 1.5 mm         |
| Type of door closing      | non keylock    |
| Interlockable             | No             |
| Cover type                | Closed (plain) |
| Door leave                | single         |
| Cover type                | Door           |
| Transparent cover or door | No             |

**Materials**

|            |                       |
|------------|-----------------------|
| Colour     | white                 |
| Colour     | white                 |
| RAL colour | RAL 9010 - Pure white |

**Installation, mounting**

|                          |    |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

**Equipment**

|                                      |     |
|--------------------------------------|-----|
| Number of rows                       | 12  |
| Quantity of section in width         | 2   |
| Number of openings for flange plates | 2   |
| Extension possible                   | Yes |

**Standards**

---

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

**Safety**

---

|   |      |
|---|------|
| IK protection code against mechanical impacts | IK10 |
|---|------|

---

|               |    |
|---------------|----|
| REACH conform | No |
|---------------|----|

---

|                 |   |
|-----------------|---|
| Fire resistance | - |
|-----------------|---|